

**Stoner****Stoner® KantStik® Sealer 1.0**  
For Sealing Tooling Surface Pores

# Major Marine Manufacturer Prefers Stoner® KantStik® Sealer 1.0™ .

A major marine manufacturer providing special composite vessels to the US Navy and US Coast Guard approved KantStik® Sealer 1.0 along with G495 FRP-SC semi-permanent release agent as their release system of choice. The process starts by applying two coats, 15-min apart of KantStik® Sealer 1.0 by wiping on without wiping off (wipe on / leave on). NO BUFFING REQUIRED. Follow by four coats, 15-min apart of G495 FRP-SC by wiping on without wiping off. Finally, apply the 5th coat of G495 FRP-SC and IMMEDIATELY wipe off while still wet.



Item # P59101



## Molder prefers KantStik Sealer 1.0 process because:

- Significant labor savings with no streaking!
- Most of the active ingredients bond to the mold surface instead of the towel.
- Unique G495 FRP-SC ensures no pre-release on difficult areas.
- Achieved 20% more releases.

KantStik® Sealer 1.0 is designed as a universal sealer that can be used with all Stoner release agents including SPC 1.0, Cure Fast 1.0, G494 FRP-QB, G495 FRP-SC, XK22-LV, Honey Wax® and TraSys® water-based products.