

## **Stoner®** KantStik Sealer 1.0 For Sealing Tooling Surface Pores

## Major Marine Manufacturer Prefers Stoner® KantStik® Sealer 1.0™

A major marine manufacturer providing special composite vessels to the US Marine Corps and US Coast Guard approved KantStik Sealer 1.0 along with G495 FRP-SC semi-permanent release agent as their release agent of choice. The process starts with appling two coats 15-min apart of KantStik Sealer 1.0 by wiping on without wiping off (wipe on / leave on). No buffing required. Follow by four coats 15-min apart of G495 FRP-SC by wiping on without wiping off. Finally, apply the 5th coat of G495 FRP-SC on wet and IMMEDIATELY wipe off.





## Molder prefers KantStik Sealer 1.0 process because:

- Significant labor savings.
- Allows active ingredients to bond on to the mold surface instead of the towel.
- Uniform high gloss finish.
- Unique G495 FRP-SC ensures no pre-release on difficult area.

KantStink Sealer 1.0 is designed as a universal sealer that can be used with all release agents including SPC 1.0, Cure Fast 1.0, G494 FRP-QB, G495 FRP-SC, XK22-LV, Honey Wax and TraSys water-based products.