

TraSys® 715 Water Based Mold Release Coating



Product Description

TraSys® 715 mold release coating is a translucent water-based dispersion for rotational molding applications. When applied to a mold, it exhibits outstanding release or anti-stick properties and has a very low coefficient of friction. It is clean, non-oily, nonstaining, chemically inert, and can function in temperatures to 260°C (500°F) or higher.

TraSys[®] 715 will meet molders' production, environmental, and safety requirements. It offers an unmatched combination of lubricity and durability, without the use of silicone oils, providing consistent release and reducing mold buildup. TraSys® 715 is solvent-free, meeting all existing and anticipated environmental regulations. Additionally, TraSys® 715 contains no alcohols that may form ammable vapors.

Uses

TraSys® **715** is ideal for rotational mold internals and other molding applications where a consistent, controlled release is desired.

Directions for Use

TraSys® 715 must be agitated before use. TraSys® 715 mold release coating should be applied to clean and dry surfaces. For maximum results, preheat the mold surface to 55-60°C (130-140°F) before application.

Recommended Procedure

- Clean mold thoroughly, using glass or plastic bead media, abrasive pads, and cleaning solvent or high pH detergent, to remove all prior mold release and other sources of contamination.
- If spraying, use spray equipment that provides a fine mist. When wiping, lightly dampen a clean cloth with TraSys® 715 after agitation. After agitation, apply lightly to the

- mold's surfaces, making certain that all areas of the mold are entirely coated.
- A minimum inner mold temperature of 132°C (270°F) is recom- mended to cure the release. This can easily be accomplished after application by running the mold empty through a full pro- duction cycle with the oven temperature at 170°C (350°F). Prop- er curing will give a bond between mold and coating that will ensure no transfer of coating to the first molded part, as well as ensure the most effective coating for durability and cycle life.
- When spot touch-ups are applied, curing the freshly coated area with a heat gun will further enhance the bond between the coating and the mold's surface. Larger applications may require a bake cycle as described above.

Storage and Handling

TraSys® **715** should be stored in a cool, dry, well ventilated area. Do not expose to freezing temperatures. Freezing will affect the physical condition, but will not damage the release effectiveness. Thaw at room temperature, and mix well before using.

Containers in use should be agitated before use and often during use. Drums will require a low rpm agitator to prevent separation in the storage container.

Breathing vapors should be avoided. If spraying, care should be taken to avoid inhaling mist or vapors, just as sprayed paint inhalation should be avoided.

Care should be taken not to expose TraSys® 715 mold release coating to open ame or intense heat. Temperatures above 260 °C (500 °F) may cause chemical breakdown, resulting in toxic fumes. Always wash hands after handling TraSys® 715 mold release coating.

Shelf Life

TraSys® 715 has a shelf life of up to 2 years from the date of manufacture printed on the container label.

Packaging

TraSys® **715** is available in:

 Cases of 4x1-gallon Part # TRA715GLXX2 5-gallon pails Part # TRA715PLXX2 · 55-gallon drum Part # TRA715DRXX1

Technical Assistance

Call: 800-227-5538 or 1 (717) 786-7355 Email: CustomerService@StonerMolding.com

Visit: StonerMolding.com

NO RISK GUARANTEE. Stoner Molding guarantees 100% satisfaction or your money back. If you're ever dissatisfied with any Stoner Molding product, simply return the unused portion for a full refund.





